


datasheet for AK 2 B 2540 I
 article number: 972405100



product description:	order number: 972 405-100
description:	Contact-protected, high-strength, wide-opening alligator clip. Clamping range up to 30mm bolt diameter. Solid wire clip, U-shaped and fine wire section. Nickel-plated brass connecting socket, pluggable with 4mm safety measuring leads.
typ:	AK 2 B 2540 I schwarz/black
system:	4mm safety system
order number:	972 405-100
clamping range:	30 mm
color	●
other color versions:	●●●●●●
technical data	
measurement category acc. to IEC 61010:	CAT II
type of contact:	clamp
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	32 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-30 °C to +90 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	

