

## 868MHz Flexible Whip Antenna

### Electrical Specifications

Frequency Range:	868-915MHz
Nominal Impedance:	50 ohm
Maximum Input Power:	50W
Polarization:	Omni
VSWR:	≤1.5
Connector:	SMA male straight or Right angle

### Mechanical Specifications

Material:	Rugged Antenna
Antenna dimensions:	108mm x 10mm Straight 105mm x 10mm Right Angle
Antenna weight:	10g
Ambient temperature:	-40 °C-+ 60 °C

**Order Code: ANT-900MS Straight**  
**ANT-900MR Right angle**

