

Han 10M-Metal Cover-Bolt-for Base



Part number	09 37 010 5405
Specification	Han 10M-Metal Cover-Bolt-for Base
HARTING eCatalogue	https://b2b.harting.com/09370105405

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han [®] M
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings for cable to cable housing Metal With fixing cord
Туре	Low construction High construction

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant



Material properties

China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	52.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055551
eCl@ss	27440208 Cap for industrial connectors