




# DIMENSIONS




# TERMINATION



# ORDERING INFORMATION

SERIES	8609	3	96	7	8	14	7	4	5	ELF
ROWS FITTED WITH CONTACTS										
ROW a b c		3	96							
ROW a - c		4	64							
ROW a b -		2	64							
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW MALE INSULATOR				7						
METHOD OF MOUNTING										
REVERSE MOUNTING - STYLE R						8				
TERMINATION										
STRAIGHT SPILL								14		
OPTIONS										
NO OPTION									7	
WITH HARPOONS										H
PERFORMANCE CLASS										
DIN 41612 CLASS 3										4
DIN 41612 CLASS 2										5
DIN 41612 CLASS 1										6
AS PER MIL C 55302 / JSS 50808										8
PITCH PER ROW										
2.54 mm										5
LEAD FREE VERSION										ELF

# PCB LAYOUT



GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

mat'l. code	SEE DWG C-8609-0000A	surface	ISO 1302 ✓	tolerance	ISO 406 ISO 1101	projection	product family	8609
ltr	ecn no dr date	tolerances unless otherwise specified	angles	linear	0.X ±0.1	mm	title	DIN REVERSE HEADER
A	104-0063 MINI 2004-09-17				0.XX ±0.1	←→		DIN 41612 STYLE R
B	105-0089 MINI 2005-05-19				0.XXX ±0.1	scale 3:2	dwg no	C-8609-2004
C	105-0174 MINI 2005-09-27	0°±2°					sheet 1 of 1	A3
D	106-0061 MINI 2006-05-31	dr	MINI K V				size	
E	108-0142 KR 2008-10-17	enr	RAKHEE G				type	Product Customer Drawing
F	108-0146 KR 2008-10-21	chr	M JACOB					
G	ELX-I-31454 MJA 2018-10-06	appd	BIJU K PAUL					
sheet index	revision	G						
	sheet	1						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093967814755ELF](#) [86094647814755ELF](#) [86093967814H55ELF](#) [86094647814765ELF](#) [86093967814745ELF](#)  
[86093967814765ELF](#) [86094647814745ELF](#) [86094647814785ELF](#) [86094647814H55ELF](#) [86093967814785ELF](#)  
[86092647814745ELF](#)