


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT1M-702Y	.24 (6.1)	.87 (22)	.043 (1.1)	.098 (2.5)	.159 (4.0)	.186 (4.7)	.188 (4.8)	4.0 (102)	18 (80)	MINIATURE	.10 (45)
PLT2S-702Y	.24 (6.1)	1.88 (48)	.055 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.40 (188)	50 (222)	STANDARD	.49 (222)
PLT3S-702Y	.39 (10)	3.00 (76)	.055 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	11.60 (295)	50 (222)	STANDARD	.76 (344)

NOTES:

- *1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
- 2) UL LISTED MAX TEMPERATURE RATING OF 257°F (125°C).
- 3) MATERIAL FLAMMABILITY RATING: UL94V-0.
- 4) EXCELLENT RESISTANCE TO MOST CHEMICALS.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL	DRAWING NUMBER	
11	4/25/13	BWG	MPH	RTFI	REVISED NOTES 1 AND 2, UPDATED DRAWING BORDER AND TITLE BLOCK.	SS-18060/11	PAN-TY CABLE TIE PLT PLENUM WIRING SERIES	W10001C0/11	W10001C0_DC/11-SS-18060_REV11	HALAR FLUOROPOLYMER COLOR: MAROON REGISTERED TRADEMARK OF Solvay Solexis, Inc.	SS-18060	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
							.X ± ---- .XXX ± .020 [.51]					
							.XX ± .02 [.5] ANGLES ± ----					
							THIRD ANGLE PROJECTION					
							DRAWN BY	DATE	CHK	SCALE	SIZE	
							C.HARVELL	08/07/91	HVP	NONE	SHT 1 OF 1	A

D10100DAY15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT2S-M702Y](#) [PLT3S-M702Y](#) [PLT3S-C702Y](#)