



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [ each ]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA11-A THRU PCA11-Z	'A' THRU 'Z'	30	300	1	10	.110" - .130"
PCA11-A-J	'A'-'J' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-K-T	'K'-'T' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-U-Z	'U'-'Z' [ 1 EA. ] '-' [ 2 EA. ] '+' [ 2 EA. ]	30	300	1	10	.110" - .130"
PCA11-0 THRU PCA11-9	'0' THRU '9'	30	300	1	10	.110" - .130"
PCA11-0-9	'0'-'9' [ 1 EA. ]	30	300	1	10	.110" - .130"
PCA11-MIN	'-'	30	300	1	10	.110" - .130"
PCA11-PLS	'+'	30	300	1	10	.110" - .130"

NOTES:

1. COLOR: WHITE WITH BLACK LEGENDS.
2. MILLIMETERS ARE IN [     ].
3. ONE SIDE PRINTED.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW THAT ONE SIDE PRINTED.	GAECN03212
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02982
3	3/28/11	RVU			ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336
2	8/11/10	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079
1	10/6/06	RVU			ADDED TOLERANCE AND REVISED TABLE.	4881
0	9/12/06	RVU			DRAWING RELEASE.	3732

TITLE <b>PCA11-* CLIP-ON WIRE MARKER</b>		CUSTOMER DRAWING	
ITEM REVISION NAME 100281DB/06		<b>PANDUIT</b>	
DATASET FILE NAME 100281DB_DS_C10351/06F			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL: <b>WHITE MARKER-ACETAL</b>	
.x ± .12 [ 3.05 ]     .xxx ± .025 [ .635 ] .xx ± .062 [ 1.57 ]     ANGLES ±		DRAWING NUMBER: <b>C10351</b>	
THIRD ANGLE PROJECTION			
DRAWN BY RVU	DATE 10/14/04	CHK JM	SCALE NTS
SHT 1 OF 1		A	

D10100DA/15

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PCA11-0](#) [PCA11-0-9](#) [PCA11-1](#) [PCA11-2](#) [PCA11-3](#) [PCA11-4](#) [PCA11-5](#) [PCA11-6](#) [PCA11-7](#) [PCA11-9](#) [PCA11-8](#)  
[PCA11-A](#) [PCA11-W](#) [PCA11-L](#) [PCA11-Z](#) [PCA11-G](#) [PCA11-J](#) [PCA11-R](#) [PCA11-D](#) [PCA11-U](#) [PCA11-A-J](#) [PCA11-H](#)  
[PCA11-PLS](#) [PCA11-E](#) [PCA11-Q](#) [PCA11-C](#) [PCA11-O](#) [PCA11-F](#) [PCA11-T](#) [PCA11-K](#) [PCA11-M](#) [PCA11-MIN](#)  
[PCA11-P](#) [PCA11-X](#) [PCA11-U-Z](#) [PCA11-Y](#) [PCA11-V](#) [PCA11-S](#) [PCA11-B](#) [PCA11-N](#) [PCA11-K-T](#) [PCA11-I](#)