

Protect It! Surge Protector with 6 Right-Angle Outlets, 6 ft. (1.83 m) Cord, 1340 Joules, Diagnostic LEDs, Metal Case

MODEL NUMBER: TLM626



Highlights

- 6 outlets / 6-ft. (1.83 m) cord
- 1340 joule rating
- Rugged metal case

Package Includes

- TLM626 surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's TLM626 surge suppressor offers complete AC surge suppression for comprehensive protection of workstations, personal computers, home stereos, televisions, VCRs, DVD players and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM626 offers 6 right-angle outlets, a 6-ft. (1.83 m) power cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing with 2 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input - 6-ft. (1.83 m) AC line cord with NEMA 5-15P plug/Output - 6 NEMA 5-15R right-angle outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Metal strip

SUPPRESSION: AC: 150V RMS Clamping/1340 joules/400V UL1449 3rd Edition

Features

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker protects against overload
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 2 transformers without blocking adjacent outlets



- Rugged metal case provides extra safety and durability
- Illuminated power switch
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332132291
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of outlets
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status



SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Antimicrobial	No
Power Cord Color	Black
Form Factors Supported	Supports floor / wall / desktop placement
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	225mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	30.48 x 11.68 x 6.35
Shipping Dimensions (hwd / in.)	12.00 x 4.60 x 2.50
Shipping Weight (kg)	0.73
Shipping Weight (lbs.)	1.60
Unit Dimensions (hwd / cm)	3.8 x 31.1 x 5.7
Unit Dimensions (hwd / in.)	1.5 x 12.25 x 2.25
Unit Weight (kg)	0.82
Unit Weight (lbs.)	1.8
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>