

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2074580003](#)
Status: **Active**
Overview:
Description: L1NK 396 Receptacle Housing, Single Row, 3 Circuits, UL 94V-0, Black

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [207458](#)
 Application Power, Wire-to-Board
 Overview l1nk_396_connector_system
 Product Name L1NK 396
 UPC 191130115570

Physical

Circuits (maximum) 3
 Color - Resin Black
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable Yes
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 1.180/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Pitch - Termination Interface 3.96mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification 2074580000-PK-000
 Product Specification 2074580000-PS-000, 2074580000-PS-CH-000,
 2074580000-PS-ES-000, 2074580000-PS-JP-000,
 2074580000-PS-SK-000, 2074580000-TS-000
 Sales Drawing 2074580000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207458](#) Series

Mates With

L1NK 396 Headers [207478](#) , [207479](#)

Use With

MarKK Crimp Terminal [455703000](#) ,
[455703002](#) , [455703050](#) , [455703052](#) .
 L1NK TPA Retainer [207459](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[207458-0003](#)