

INFRARED THERMOMETER

IR TEMPERATURE:

32°C~42°C
89°F~108°F

■ MS6592P

Specifications	Range	Accuracy
Temperature	32°C~42°C	±0.4°C
Resolution		0.1°C
Accuracy: Assumes ambient operating temperature (23°C ± 2°C)		32°C ~ 42°C (±0.4°C)
Features		
Spectral Response	8-14 μm	•
Measurement Distance	5-15 cm	•
Ambient Operating	15°C~35°C	•
Response Time	approx 1s	•
Relative Humidity	10%~90%	•
Display Backlight		•
Reading Hold		•
LBD	Low Battery Display	•
General		
Power Supply	2x1.5V AAA Battery	
Product Size	143mm×99mm×47mm	

