

Joystick Switch

Q-10525

TYPE: **CS-201**

SPECIFICATIONS

Rating:	4A 600V AC
Position	2
Action Type	Self-locking
Material	Plastic, Rubber, Metal
Contact Type	SPST 4NO
Max. Isolation Voltage	AC 600V
Delination Angle	30 Degree
Fit for Mount Panel Thickness(Max.)	8mm/0.3"
Mount Panel Cutout Diameter	29mm/1.1"
Lever Length	7cm/ 2.8"
Operating Temperature:	-25°C ~ +100°C
Net Weight	176g

