

rotronic

Datenblatt - Fiche technique - Data sheet

11.02.8802




ROLINE Gold USB 2.0 Kabel, Typ A-B, 1,8m

ROLINE Câble USB 2.0 Gold, Type A-B, 1,8m

ROLINE Gold USB 2.0 Cable, Type A-B, 1.8 m

ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE



NOTES:

1.CABLE:

UL-2725 [28AWG(7/0.127 T.C)*1P+24AWG(7/0.203 T.C)*2C +AL/MY+DRAIN WIRE+65% BRAID] PVC JACKET, OD:φ4.7±0.15mm COLOR:BLACK(NK-K01)REV 2.0.

2.CONNECTER:

P1:USB A TYPE MALE GOLD PLATED 30u" CONTACT, GOLD PLATED SHELL, REV 2.0.

P2:USB B TYPE MALE GOLD PLATED 30u" CONTACT, GOLD PLATED SHELL, REV 2.0.

3.HOOD:P1&P2:ASS'Y TYPE,ALUMINUM HOOD GOLD PLATED.

SR:MOLDED TYPE,PVC 30P,COLOR:BLACK(NK-K01)

4.ELECTRICLE TEST:

<1>100% OPEN SHORT & MIS WIRE TEST.

<2>CONTACT RESISTANCE 3 Ohms MAX.

<3>INSULATION RESISTANCE 10M Ohms MIN.

5.PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.

DWG	P/N	L(mm)	T(mm)	PCS/INNER CARTON	PCS/CARTON
170-3998-3	11.02.8805-5	4500	50	5	10
170-3998-2	11.02.8803-10	3000	30	10	20
170-3998-1	11.02.8802-10	1800	30	10	40

	P1		P2
RED	1	_____	1 VCC
WHITE	2	_____	2 -DATA
GREEN	3	_____	3 +DATA
BLACK	4	_____	4 GROUND
SHELL		_____	SHELL

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw FANNIE 12/10/10'

Chek

Engr

Rotronic co., LTD.

Title: ROLINE Gold USB 2.0 Cable, Type A-B

Customer P/N: 11.02.8802 / 11.02.8803 / 11.02.8805

App'd _____ Customer _____

Scale NONE Units m/m Third Angle Projection

Dwg No. 170-3998 REV: A Sheet 1/1