

- Product List
- Test Lead Builder
- Brand Cross
- Where to Buy
- Product Releases
- Contact Us
- Service
- About

## CT3978B : Probe Body w/Locking Cap & Full Accessories, UL, B/R Pairs

Probe Body w/Locking Cap & Full Accessories, UL, B/R Pairs

Pair of DMM probe bodies with 2 mm (.080") diameter x 19 mm (0.75") probe tips for all test applications. With locking cap installed, the probe meets 600 V CAT IV applications. Remove the safety cap for access to the standard 2mm tip and to attach tip accessories.

Includes pairs of extended tips, alligator clips, spade lugs and sprung hooks all featuring "snap-locks" to probes.

Features:

- Probe bodies with 4 mm sheathed banana jack connections
- UL 61010-031 rated
- Accessories "snap-lock" to probe bodies
- Cap on probe tip provides CAT III / CAT IV usage

Kit Contains:

- (2) Probe Bodies, black & red - (CT3975B)
- (2) Extended Tips, black & red - (CT3941B)
- (2) Alligator Clips, black & red - (CT3943B)
- (2) Spade Lugs, black & red - (CT3945B)
- (2) Sprung Hooks, black & red - (CT3947B)



Values	Probe Bodies	Extended Tips	Alligator Clips	Spade Lugs	Sprung Hooks
Voltage UL 61010-031	1,000 V CAT III / 600 V CAT IV w/cap 1,000 V CAT II w/o	300 V CAT II	300 V CAT II	<30 Vac / <60 Vdc	300 V CAT II
Current	10 A	3 A	5 A	5 A	3 A
Temperature	-20° to +80°C				
RoHS 2 (2011/65/EU)	Compliant				

- [MANUAL](#)
- [TIP ADAPTER MANUAL](#)

Model	Where To Buy
CT3978B	<a href="#">CONTACT</a>