

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300660069](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower A-Size (7/8"-M22) Receptacle, 4 Poles, Female, 1/2" - 14 NPT, 14/1 AWG, 0.5m (19.7") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family Industrial Receptacles  
 Series [130066](#)  
 IP Rating IP67  
 Overview [BradPower Cordsets and Receptacles](#)  
 Product Name BradPower A-Size  
 Type Single Ended (pigtail)  
 UPC 78678856635

**Physical**

Coupling Type Internal Thread  
 Gender Female  
 Keyway Single  
 Length 0.50m  
 Material - Component Black Anodized Aluminum  
 Mounting Thread Size 1/2" - 14 NPT  
 Net Weight 111.000/g  
 Orientation Straight  
 Panel Mount Back, Front  
 Poles 4  
 Temperature Range - Operating -20°C to +90°C  
 Wire Size AWG 14  
 Wire/Cable Type THHN

**Electrical**


Current - Maximum per Contact 15.0A  
 Voltage - Maximum 600V

**Material Info**

Engineering Number 1R4000A28M005G

**Reference - Drawing Numbers**

Sales Drawing SD-130066-076-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
 D(2020)9139-DC (19 Jan 2021)  
 Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>), barium salt (1:1), lead-diethyl sulphate  
 Acetamide, N-methyl-Dinoseb  
 1-bromopropane  
 furan  
 tricosafuorododecanoic acid  
 heptacosafuorotetradecanoic acid  
 methoxyacetic acid  
 1,2-diethoxyethane  
 henicosafluoroundecanoic acid  
 sodium  
 peroxometaborate  
 pentacosafuorotridecanoic acid  
 3-ethyl-2-methyl-2-(3-methylbutyl)-1,3-oxazolidi  
 Hydrazine  
 Hexabromocyclododecane (HBCDD)  
 Trixylyl phosphate  
 4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated  
 Methylhexahydrophthalic anhydride  
 Sodium perborate; perboric acid, sodium salt

**China RoHS**

Cadmium-chloride  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Arsenic acid  
(H3AsO4), triethyl  
ester  
Diarsenic-pentaoxide  
Diarsenic-trioxide  
5-tert-Butyl-2,4,6-  
trinitro-m-xylene  
2,4-Dinitrotoluene  
1-Methyl-2-  
pyrrolidone  
formamide  
4,4'-  
bis(dimethylamino)benzophenone  
N,N,N',N'-  
tetramethyl-4,4'-  
methyldianiline  
1,2-bis(2-  
methoxyethoxy)ethane  
[4-[4,4'-  
bis(dimethylamino)  
benzhydrylidene]cycl  
4,4'-  
bis(dimethylamino)-4"-  
(methylamino)trityl  
Diboron-trioxide  
[4-[[4-Anilino-1-  
naphthyl][4-  
(dimethylamino)phen  
 $\alpha,\alpha$ #Bis[4-  
(dimethylamino)phenyl]-4  
(phenylamino)

Lead

Cadmium-chloride

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130066 Series](#)

This document was generated on 07/07/2021

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130066-0069](#)