


# TEMP-FLEX


a **molex** company

## INSULATION DISPLACEMENT CABLE: 0.050" PITCH, 28 AWG, STRANDED EXTRUDED FEP

### PART NUMBER DESCRIPTION



### MECHANICAL CHARACTERISTICS



Number of Conductors	Span	Width
10	0.450 ± .007	0.500 ± .007
14	0.650 ± .007	0.700 ± .007
15	0.700 ± .007	0.750 ± .007
16	0.750 ± .007	0.800 ± .007
20	0.950 ± .010	1.000 ± .010
24	1.150 ± .010	1.200 ± .010
25	1.200 ± .010	1.250 ± .010
26	1.250 ± .010	1.300 ± .010
30	1.450 ± .010	1.500 ± .010
34	1.650 ± .010	1.700 ± .010
37	1.800 ± .010	1.850 ± .010
40	1.950 ± .010	2.000 ± .010
50	2.450 ± .010	2.500 ± .010
60	2.950 ± .012	3.000 ± .015
64	3.150 ± .012	3.200 ± .015

<b>Impedance (ohms)</b>	115 Unbalanced	165 Balanced
<b>Capacitance (pF/ft)</b>	10.5 Unbalanced	6.0 Balanced
<b>Inductance (uH/ft)</b>	0.14 Unbalanced	0.16 Balanced
<b>Propagation delay (ns/ft)</b>	1.22	
<b>Velocity of propagation (%)</b>	83	
<b>Insulation resistance (meg-ohm)</b>	>500	
<b>Voltage rating</b>	300V	
<b>Temperature rating</b>	200C	
<b>Conductor Type</b>	<b>Standard:</b> 28 AWG, 7/36, Silver Plated Copper <b>Optional:</b> 28 AWG, 19/40, Silver Plated Copper	
<b>Insulation</b>	FEP	
<b>Number of Conductors</b>	10 to 64	
<b>Color</b>	<b>Standard:</b> Solid red or blue with blue polarity stripe <b>Optional:</b> Rainbow	

### STANDARD PACKAGING

100 ft./Reel, 50 Ft. minimum average length, 10 Ft. minimum length  
UL STYLE 20424

### MINIMUM ORDER QUANTITY:

500ft

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[F2807S-10-050-55](#) [F2807S-20-050-55](#) [F2807S-26-0394-55](#) [F2807S-50-0394-55](#) [F2807S-14-050-55](#) [F2807S-44-0394-55](#) [100057-0203](#) [100057-0201](#) [100057-0034](#) [100057-0151](#) [100057-0031](#) [100057-0174](#)