

Catalogue Export

SNA Europe




-1. Sockets & accessories

-1.1. SOCKETS 1/4"

- Standard length sockets, 1/4" square drive
- Hex profile, metric sizes
- Not suitable for machine operation
- High performance alloy steel
- High polished finish
- Knurled
- ISO 2725 / 1174
- DIN 3124 / 3120
- SB = Retail packed on a plastic info card

Hexagon Metric

6700SM

				L mm	D1 mm	D2 mm	
6700SM-4	7314151087944	5	4	24.7	6.8	11.9	9
6700SM-4.5	7314151087951	5	4.5	24.7	7.4	11.9	10
6700SM-5	7314151087968	5	5	24.7	8.1	11.9	10
6700SM-5.5	7314151087975	5	5.5	24.7	8.7	11.9	10
6700SM-6	7314151087982	5	6	24.7	9.3	11.9	10
6700SM-7	7314151087999	5	7	24.7	10.8	11.9	12
6700SM-8	7314151088002	5	8	24.7	11.9	11.9	12
6700SM-9	7314151088019	5	9	24.7	13.4	12.4	12
6700SM-10	7314151088026	5	10	24.7	14.5	13	15
6700SM-11	7314151088033	5	11	24.7	15.9	14.1	18
6700SM-12	7314151088040	5	12	24.7	16.9	15	18
6700SM-13	7314151088057	5	13	24.7	18	15.6	20
6700SM-14	7314151088064	5	14	24.7	19.6	16	22
SB6700SM-4	7314150104307	1	4	24.7	6.8	11.9	9
SB6700SM-4.5	7314150104314	1	4.5	24.7	7.4	11.9	10
SB6700SM-5	7314150104321	1	5	24.7	8.1	11.9	10
SB6700SM-5.5	7314150104338	1	5.5	24.7	8.7	11.9	10
SB6700SM-6	7314150104345	1	6	24.7	9.3	11.9	10
SB6700SM-7	7314150104352	1	7	24.7	10.8	11.9	12
SB6700SM-8	7314150104369	1	8	24.7	11.9	11.9	12
SB6700SM-9	7314150104376	1	9	24.7	13.4	12.4	12
SB6700SM-10	7314150104383	1	10	24.7	14.5	13	15
SB6700SM-11	7314150104390	1	11	24.7	15.9	14.1	18
SB6700SM-12	7314150104406	1	12	24.7	16.9	15	18
SB6700SM-13	7314150104413	1	13	24.7	18	15.6	20
SB6700SM-14	7314150104420	1	14	24.7	19.6	16	22