



PART NUMBERS	CABLE LENGTH "X"
DB25M02DB25M	2.00 FT +/- 1.50 IN
DB25M05DB25M	5.00 FT +/- 1.50 IN
DB25M10DB25M	10.00 FT +/- 1.50 IN
DB25M15DB25M	15.00 FT +/- 1.50 IN

CUSTOMER DRAWING

- NOTES:
1. THE PRODUCT COMES COILED AND PACKAGED IN A BAG.
 2. JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (4) AND #M3 THREAD (4) JACKSCREWS.
 3. MATERIALS:
 DSUB - COPPER ALLOY, NICKEL PLATED WITH GOLD PINS
 CABLE - COPPER, THERMOPLASTIC
 JACKSCREWS - STAINLESS STEEL
 4. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
C	26795	7-8-11	TO	TJK
B	26637	10/4/10	RS	TJK
A	25716	10/03/07	JGK	TJK

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
 - TWO PLACE DECIMALS ±0.02
 - THREE PLACE DECIMALS ±0.005

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH					MATERIAL				
SPEC No.					SPEC No.				
FIRST USED ON					SCALE				
					1:1				
DATE DRAWN	BY	CHKD	APVD						
9/5/2006	JGK	RS	TJK						
			11/19/10	11/19/10					
NAME					PART No.				
DB25M TO DB25M, RoHS					DB25M__DB25M				
					REV				
					C				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25M10DB25M](#)