

Specifications	Range
<b>Model</b>	<b>UT302A</b>
Temperature Range	-32°C ~ 450°C
	-26°F ~ 842°F
Accuracy	±1.8°C or ±1.8%
Repeatability	±0.5°C or ±0.5%
Resolution	0.1°C/0.1°F
Distance to Spot Size	20:01
Response Time	250ms (95% of reading)
Emissivity	0.10 ~ 1.0 Adjustable
Laser Type	Class 2 ( II )
Laser Power	<1mW
Laser Wavelength	630nm ~ 670nm
Spectral Response	8μm ~ 14μm
<b>Features</b>	
°C/°F Selections	√
Laser switch	√
Display Hold (s)	8 seconds
Auto Power Off	√
Low Battery Indication	√

MAX Mode	√
MIN Mode	√
DIFF Mode	√
AVG Mode	√
LCD Backlight	√
Electricity Cut-off Memory	√
Tripod Mount	√
<b>General Characteristics</b>	
Power	9V battery (6F22)
LCD Size	32mm X 29mm
Product Color	Red and grey
Product Net Weight	322g
Product Size	169mm X 138mm X 53mm
Standard Accessories	Battery
Standard Individual Packing	Blister, English Manual, Carrying Bag
Standard Quantity Per Carton	20pcs
Standard Carton Measurement	605×360×468mm (0.101 CBM Per Standard Carton)

Standard Carton Gross Weight	12.4kg
------------------------------	--------