





Cable Ties for outdoor use (UV-resistant)

T-Series in PA66W black



TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Tools	Article-No.
T120R(E)	7.6	387.0	100.0	535	PA66W	Black (BK)	100 pcs.	3;9-12	111-12060
T120M	7.6	460.0	125.0	535	PA66W	Black (BK)	100 pcs.	3;9-12	111-12660
T120L	7.6	760.0	225.0	535	PA66W	Black (BK)	50 pcs.	3;9-12	111-12430
T150M	8.9	530.0	150.0	780	PA66UV	Black (BK)	25 pcs.	9-12	111-15660
T150L	8.9	820.0	243.8	780	PA66UV	Black (BK)	25 pcs.	9-12	111-15460
T150XL	8.9	1,095.0	330.2	780	PA66UV	Black (BK)	25 pcs.	9-12	111-15502
T150XLL	8.9	1,325.0	406.4	780	PA66UV	Black (BK)	25 pcs.	9-12	111-15305
T250R	12.4	515.0	124.5	1,115	PA66HIRHSUV	Black (BK)	25 pcs.	11-12	111-24805

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools											
	2	3	4	5	6	7	8	9	10	11	12
	MK20	MK21	MK3SP	MK3PNSP2	EVO7	MK7HT	MK7P	MK6	EVO9	EVO9HT	MK9P
	545	545	546	546	548	549	550	551	549	549	552

For more information on toolings please refer to the Application Tooling chapter.