

EURONORD P 121209



Sample photo

Order symbol: P 121209
Product nbr: 7094220
Description: Enclosure
Remarks: Polyester

EAN: 6418074004376
EI. number:
 Finland: 3423660
 Electric No. 8212005646
 Denmark:
 Electric No. Italy: 7331030
 Electric No. Sweden: 2536215

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	122	120	90	Ingress Protection (EN 60529): IP66
inch:	4.8	4.7	3.5	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polyester			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7001			UV resistance: UL 508
Cover screws material:	Stainless steel			Flammability Rating: UL 94 V0
Cover colour:	RAL 7001			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:				
Temperature °C (short term):	-50 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-60 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

