



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.2mm 00.= ±0.4mm

Housing Material : Polyamide (PA66), flame-retardant to UL 94V-2

Current : 24A(IEC)

Voltage : 450V(IEC)

Working Temp : T110(IEC)

Wire Range : Installation side: 0.75 ~ 2.5mm², sol.
Lighting side: 0.5 ~ 2.5mm², sol/Str.

Stripping Length : 9 ~ 11mm(0.35 ~ 0.43inch)

 金筆企業股份有限公司
HEAVY POWER CO., LTD.

TITLE :
EASY-LNIK LIGHTING CONNECTORS
Model No. PC302
Part No. PC302

Drawn By

Rev.

International Approvals
VDE, FIMKO, KEMA, CEBEC

kuan
2017.06.26

A2