



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.2mm 00.= ±0.4mm

Housing Material : UL 94V-0 Polycarbonate
 Terminal Insert : (1) Tin plated copper
 (2) Spring plate: Steel
 Current : 24A(IEC)
 Voltage : 600V(UL), 450V(IEC)
 Working Temperature : T85(IEC), 105° C(UL)
 Stripping Length : 11.0mm(0.43 inch)
 Wire Range : 0.5-2.5mm² Rigid Sol / 1.0-2.5mm² Rigid Str(IEC)
 22-12AWG, Sol .Cu / 18-12AWG, Str. Cu / 22-14AWG, Tin-dipped Str. Cu(UL)

 金筆企業股份有限公司
 HEAVY POWER CO., LTD.

TITLE :
 PUSH-IN WIRE CONNECTORS
 Model No. PC352X
 Part No. PC352X

Drawn By _____ Rev. _____

International Approvals
 cULus, CE, ENEC, FIMKO, NEMKO, SEMKO, PSE, CQC

kuan
 2017.07.04

A4