



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.2mm 00.= ±0.4mm

Housing Material : UL 94V-0 Polycarbonate

Terminal Insert : (1) Tin plated copper  
(2) Spring plate: Steel

Current : 24A(IEC)

Voltage : 600V(UL), 450V(IEC)

Working Temperature : T85(IEC), 105° C(UL)

Stripping Length : 11.0mm(0.43 inch)

Wire Range : 0.5-2.5mm<sup>2</sup> Rigid Sol / 1.0-2.5mm<sup>2</sup> Rigid Str(IEC)  
22-12AWG, Sol. Cu / 18-12AWG, Str. Cu / 22-14AWG, Tin-dipped Str. Cu(UL)

 金筆企業股份有限公司  
HEAVY POWER CO., LTD.

TITLE :  
PUSH-IN WIRE CONNECTORS

Model No. PC355X

Part No. PC355X

Drawn By

Rev.

International Approvals

cULus, CE, ENEC, FIMKO, NEMKO, SEMKO, PSE, CQC

*kuan*  
2017.07.04

A4