

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030114](#)
Status: **Active**
Overview:
Description: Krimptite Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19203](#)
 Comments 1200° F (649° C)
 Crimp Quality Equipment Yes
 Overview high_temperature_temp_terms_terminals
 Product Name Krimptite, Temp-Terms
 Type Ring
 UPC 800753050235

Physical

Barrel Type Closed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 1.326/g
 Packaging Type Adhesive Tape on Reel
 Stud Size 10 (M5)
 Wire Size AWG 10, 12
 Wire Size mm² 4.00-6.00

Material Info

Engineering Number C-U-128-10T

Reference - Drawing Numbers

Product Specification PS-19902-011-001
 Sales Drawing CCD10104, SD-19069-020-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19203](#) Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088
Mini-Mac Applicator	638851000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0114](#)