

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500113](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Crimp Terminal, 22-30 AWG, Hot Tin (Sn) Dip Plating

Documents:

Drawing (PDF)	Packaging Specification PK-2759-002-001 (PDF)
Product Specification 50510002-PS-000 (PDF)	Test Summary TS-10-07-001 (PDF)
Product Specification PS-10-07-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	2759
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08500114 (Loose)
Product Name	KK 254
UPC	800753614444

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.065/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm ²	N/A

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Engineering Number	2759-(P909)B
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-002-001
Product Specification	50510002-PS-000, PS-10-07-001
Sales Drawing	SD-2759
Test Summary	TS-10-07-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[2759 Series](#)

Use With

[2695](#) , [5051](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	11030022
Terminator Die	11402265
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	638120000
Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30	638882000

AWG Wire with
Insulation Diameter
1.09-1.57mm
and 22-28
AWG Wire with
Insulation Diameter
1.20-1.70mm
Mini-Mac Applicator [638882100](#)
for KK and Cat Ear
Terminals for 22-30
AWG Wire with
Insulation Diameter
0.96-1.20mm

This document was generated on 07/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-50-0113](#) [08-50-0113 \(Mouser Reel\)](#) [08-50-0113 \(Cut Strip\)](#)