


B.2: Valide



Notes :

- Machined contact
- Extraction tool : RX20D44

Material :

- Contact body:high conductive copper alloy
- :plating : 0.4 micron gold over nickel on active part
- Retaining spring:stainless steel

Performance Characteristics :

- Contact retention in the body:50N max
- Contact insertion force:5N max
- Contact separation force:0.30N min
- Current rating:7.5 Amps
- Contact resistance:6mΩ max
- Dielectric withstanding voltage:1500 Vrms min
- For RCXXW3K : Wire strip lenght : 4,8 mm

Part Number	Fig.	Insulation Diameter (mm)	WIRE SIZE		Ø A	HAND CRIMP TOOLING			B	C
			AWG	MM ²		SHANDLES	MH860			
						Tool Head	Locator	Selector		
RC18W3K	1	Ø 1,20 - 2,10	20 -18	0,50 - 0,82	Ø 1,97	S20RCM	MH86301	6 / 8	/	/
RC20W3K	2	Ø 1,20 - 1,60	22 - 20	0,32 - 0,50	Ø 1,86			5 / 7	/	/
RC24W3K	3	Ø 0,90 - 1,60	26 - 24	0,12 - 0,25	Ø 1,53			5 / 6	/	/
RCW50A7K	4	/	/	/	/	/	/	/	18,1	9,90
RCW5016K	5	/	/	/	/	/	/	/	18,74	6,70

P/N : SEE TABLE

B	18/07/2018	Correct mistakes : separation force: 2N replace by 0.30N min	25144
ISS	DATE	Latest modification - by:	ROUILLARD Ch MOD N°
Designed by:		CHARLOT MA Date: 14/09/12	CUSTOMER DRAWING
TITLE		SPILL AND CRIMP SOCKET CONTACT AWG 20 CONNECTOR UTOW	
Scale		Dimensions in mm General linear Tolerances: ± --	NPRDS / PROJECT RC
7/1		This document is the property of SOURIAU It must not be reproduced or communicated without permission	
FORMAT		SOURIAU DRG N° RCXWXC-C	
A2	SHEET		1 / 1

Country	Jurisdiction & Control List
FR	NOT LISTED

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Souriau:](#)

[RC18W3K](#)