

Device Name	Device Pin Count	Program Memory	CPU Speed	RAM (Bytes)	mikroICD Supported
PIC10F200	6	0.375	4	16	No
PIC10F202	6	0.75	4	24	No
PIC10F204	6	0.375	4	16	No
PIC10F206	6	0.75	4	24	No
PIC10F220	6	0.375	8	16	No
PIC10F222	6	0.75	8	23	No
PIC12F508	8	0.75	4	25	No
PIC12F509	8	1.5	4	41	No
PIC12F510	8	1.5	8	38	No
PIC12F609	8	1.75	20	64	No
PIC12HV609	8	1.75	20	64	No
PIC12F615	8	1.75	20	64	No
PIC12HV615	8	1.75	20	64	No
PIC12F629	8	1.75	20	64	No
PIC12F635	8	1.75	20	64	No
PIC12F675	8	1.75	20	64	No
PIC12F683	8	3.5	20	128	No
PIC16F54	18	0.75	20	25	No
PIC16F57	28	3	20	72	No
PIC16F59	40	3	20	134	No
PIC16F72	28	3.5	20	128	No
PIC16F73	28	7	20	192	No
PIC16F74	40	7	20	192	No
PIC16F76	28	14	20	368	No
PIC16F77	40	14	20	368	No
PIC16F83	18	0.875	20	36	No
PIC16F84	18	1.75	20	68	No
PIC16F84A	18	1.75	20	68	No
PIC16F87	18	7	20	368	No
PIC16F88	18	7	20	368	No
PIC16F505	14	1.5	20	72	No
PIC16F506	14	1.5	20	67	No
PIC16F526	14	1.5	20	67	No
PIC16F610	14	1.75	20	64	No
PIC16HV610	14	1.75	20	64	No
PIC16F616	14	3.5	20	128	No
PIC16HV616	14	3.5	20	128	No
PIC16F627	18	1.75	20	224	No
PIC16F627A	18	1.75	20	224	No
PIC16F628	18	3.5	20	224	No
PIC16F628A	18	3.5	20	224	No
PIC16F648A	18	7	20	256	No
PIC16F630	14	1.75	20	64	No
PIC16F631	20	1.75	20	64	No
PIC16F636	14	3.5	20	128	No
PIC16F639	20	3.5	20	128	No
PIC16F676	14	1.75	20	64	No
PIC16F677	20	3.5	20	128	No
PIC16F684	14	3.5	20	128	No

PIC16F685	20	7	20	256	No
PIC16F687	20	3.5	20	128	No
PIC16F688	14	7	20	256	No
PIC16F689	20	7	20	256	No
PIC16F690	20	7	20	256	No
PIC16F716	18	3.5	20	128	No
PIC16F722	28	3.5	20	128	Yes
PIC16LF722	28	3.5	20	128	Yes
PIC16F723	28	7	20	192	Yes
PIC16F724	40	7	20	192	Yes
PIC16F726	28	14	20	368	Yes
PIC16F727	40	14	20	368	Yes
PIC16F737	28	7	20	368	Yes
PIC16F747	40	7	20	368	Yes
PIC16F767	28	14	20	368	Yes
PIC16F777	40	14	20	368	Yes
PIC16F785	20	3.5	20	128	No
PIC16HV785	20	3.5	20	128	No
PIC16F818	18	1.75	20	128	Yes
PIC16F819	18	3.5	20	256	Yes
PIC16F870	28	3.5	20	128	Yes
PIC16F871	40	3.5	20	128	Yes
PIC16F872	28	3.5	20	128	Yes
PIC16F873	28	7	20	192	Yes
PIC16F873A	28	7	20	192	Yes
PIC16F874	40	7	20	192	Yes
PIC16F874A	40	7	20	192	Yes
PIC16F876	28	14	20	368	Yes
PIC16F876A	28	14	20	368	Yes
PIC16F877	40	14	20	368	Yes
PIC16F877A	40	14	20	368	Yes
PIC16F882	28	3.5	20	128	Yes
PIC16F883	28	7	20	256	Yes
PIC16F884	40	7	20	256	Yes
PIC16F886	28	14	20	368	Yes
PIC16F887	40	14	20	368	Yes
PIC16F913	28	7	20	256	Yes
PIC16F914	40	7	20	256	Yes
PIC16F916	28	14	20	352	Yes
PIC16F917	40	14	20	352	Yes
PIC16F946	64	14	20	336	Yes
PIC16F1518	28	28	20	1024	Yes
PIC16F1828	20	7	32	256	Yes
PIC16F1933	28	7	32	256	Yes
PIC16F1934	40	7	32	256	Yes
PIC16F1936	28	14	32	512	Yes
PIC16F1937	40	14	32	512	Yes
PIC16F1938	28	28	32	1024	Yes
PIC16F1939	40	28	32	1024	Yes
PIC16F1946	64	14	32	512	Yes
PIC16F1947	64	28	32	1024	Yes

PIC18F13K22	20	8	64	256	Yes
PIC18LF13K22	20	8	64	256	Yes
PIC18F13K50	20	8	48	512	Yes
PIC18LF13K50	20	8	48	512	Yes
PIC18F14K22	20	16	64	512	Yes
PIC18LF14K22	20	16	64	512	Yes
PIC18F14K50	20	16	48	768	Yes
PIC18LF14K50	20	16	48	768	Yes
PIC18F23K20	28	8	64	512	Yes
PIC18F23K22	28	8	64	512	Yes
PIC18LF23K22	28	8	64	512	Yes
PIC18F24K20	28	16	64	768	Yes
PIC18F24K22	28	16	64	768	Yes
PIC18LF24K22	28	16	64	768	Yes
PIC18F25K20	28	32	64	1536	Yes
PIC18F25K22	28	32	64	1536	Yes
PIC18LF25K22	28	32	16	1536	Yes
PIC18F26K20	28	64	64	3936	Yes
PIC18F26K22	28	64	64	3896	Yes
PIC18LF26K22	28	64	64	3896	Yes
PIC18F43K20	40	8	64	512	Yes
PIC18F43K22	40	8	64	512	Yes
PIC18LF43K22	40	8	64	512	Yes
PIC18F44K20	40	16	64	768	Yes
PIC18F44K22	40	16	64	768	Yes
PIC18LF44K22	40	16	64	768	Yes
PIC18F45K20	40	32	64	1536	Yes
PIC18F45K22	40	32	64	1536	Yes
PIC18LF45K22	40	32	64	1536	Yes
PIC18F46K20	40	64	64	3936	Yes
PIC18F46K22	40	64	64	3896	Yes
PIC18LF46K22	40	64	64	3896	Yes
PIC18F46K80	44	64	48	3648	Yes
PIC18F1220	18	4	40	256	Yes
PIC18F1230	18	4	40	256	Yes
PIC18F1320	18	8	40	256	Yes
PIC18F1330	18	8	40	256	Yes
PIC18F2220	28	4	40	512	Yes
PIC18F2221	28	4	40	512	Yes
PIC18F2320	28	8	40	512	Yes
PIC18F2321	28	8	40	512	Yes
PIC18F2331	28	8	40	768	Yes
PIC18F2410	28	16	40	768	Yes
PIC18F242	28	16	40	768	Yes
PIC18F2420	28	16	40	768	Yes
PIC18F2423	28	16	40	768	Yes
PIC18F2431	28	16	40	768	Yes
PIC18F2439	28	12	40	640	Yes
PIC18F2450	28	16	48	768	Yes
PIC18F2455	28	24	48	2048	Yes
PIC18F2458	28	24	48	2048	Yes

PIC18F248	28	16	40	768	Yes
PIC18F2480	28	16	40	768	Yes
PIC18F2510	28	32	40	1536	Yes
PIC18F2515	28	48	40	3968	Yes
PIC18F252	28	32	40	1536	Yes
PIC18F2520	28	32	40	1536	Yes
PIC18F2523	28	32	40	1536	Yes
PIC18F2525	28	48	40	3968	Yes
PIC18F2539	28	24	40	1408	Yes
PIC18F2550	28	32	48	2048	Yes
PIC18F2553	28	32	48	2048	Yes
PIC18F258	28	32	40	1536	Yes
PIC18F2580	28	32	40	1536	Yes
PIC18F2585	28	48	40	3328	Yes
PIC18F2610	28	64	40	3968	Yes
PIC18F2620	28	64	40	3968	Yes
PIC18F2680	28	64	40	3328	Yes
PIC18F2682	28	80	40	3328	Yes
PIC18F2685	28	96	40	3328	Yes
PIC18F4220	40	4	40	512	Yes
PIC18F4221	40	4	40	512	Yes
PIC18F4320	40	8	40	512	Yes
PIC18F4321	40	8	40	512	Yes
PIC18F4331	40	8	40	768	Yes
PIC18F4410	40	16	40	768	Yes
PIC18F442	40	16	40	768	Yes
PIC18F4420	40	16	40	768	Yes
PIC18F4423	40	16	40	768	Yes
PIC18F4431	40	16	40	768	Yes
PIC18F4439	40	12	40	640	Yes
PIC18F4450	40	16	48	768	Yes
PIC18F4455	40	24	48	2048	Yes
PIC18F4458	40	24	48	2048	Yes
PIC18F448	40	16	40	16	Yes
PIC18F4480	40	16	40	768	Yes
PIC18F4510	40	32	40	1536	Yes
PIC18F4515	40	48	40	3968	Yes
PIC18F452	40	32	40	1536	Yes
PIC18F4520	40	32	40	1536	Yes
PIC18F4523	40	32	40	1536	Yes
PIC18F4525	40	48	40	3968	Yes
PIC18F4539	40	24	40	1408	Yes
PIC18F4550	40	32	48	2048	Yes
PIC18F4553	40	32	48	2048	Yes
PIC18F458	40	32	40	1536	Yes
PIC18F4580	40	32	40	1536	Yes
PIC18F4585	40	48	40	3328	Yes
PIC18F4610	40	64	40	3968	Yes
PIC18F4620	40	64	40	3968	Yes
PIC18F4680	40	64	40	3328	Yes
PIC18F4682	40	80	40	3328	Yes

PIC18F4685	40	96	40	3328	Yes
PIC18F24J10	28	16	40	1024	Yes
PIC18F24J11	28	16	48	3800	Yes
PIC18F24J50	28	16	48	3800	Yes
PIC18F25J10	28	32	40	1024	Yes
PIC18F25J11	28	32	48	3800	Yes
PIC18F25J50	28	32	48	3800	Yes
PIC18F26J11	28	64	48	3800	Yes
PIC18F26J50	28	64	48	3800	Yes
PIC18F26J53	28	64	48	3800	Yes
PIC18F27J53	28	128	48	3800	Yes
PIC18F44J10	40	16	40	1024	Yes
PIC18F44J11	44	16	48	3800	Yes
PIC18F44J50	44	16	48	3800	Yes
PIC18F45J10	40	32	40	1024	Yes
PIC18F45J11	44	32	48	3800	Yes
PIC18F45J50	44	32	48	3800	Yes
PIC18F46J11	44	64	48	3800	Yes
PIC18F46J50	44	64	48	3800	Yes
PIC18F46J53	44	64	48	3800	Yes
PIC18F47J53	44	128	48	3800	Yes
PIC18LF24J10	28	16	40	1024	Yes
PIC18LF24J11	28	16	48	3800	Yes
PIC18LF24J50	28	16	48	3800	Yes
PIC18LF25J10	28	32	40	1024	Yes
PIC18LF25J11	28	32	48	3800	Yes
PIC18LF25J50	28	32	48	3800	Yes
PIC18LF26J11	28	64	48	3800	Yes
PIC18LF26J50	28	64	48	3800	Yes
PIC18LF26J53	28	64	48	3800	Yes
PIC18LF27J53	28	128	48	3800	Yes
PIC18LF44J10	40	16	40	1024	Yes
PIC18LF44J11	44	16	48	3800	Yes
PIC18LF44J50	44	16	48	3800	Yes
PIC18LF45J10	40	32	40	1024	Yes
PIC18LF45J11	44	32	48	3800	Yes
PIC18LF45J50	44	32	48	3800	Yes
PIC18LF46J11	44	64	48	3800	Yes
PIC18LF46J50	44	64	48	3800	Yes
PIC18LF46J53	44	64	48	3800	Yes
PIC18LF47J53	44	128	48	3800	Yes