








HARAX® Circular connector M8



Circular Connectors

Identification	Part No.		Drawing	Dimensions in mm
	Male	Female		
<p>HARAX® M8-XS</p> <p>straight version, 3-poles for 0.1 - 0.14 mm²</p> 	21 02 159 1305		 <p>Gesamtlänge im verschraubten Zustand ca. 40,8mm Complete length when assembled app. 40,8mm</p> <p>Kabelø 1,9-2,5mm cableø 1,9-2,5mm</p> <p>Kabelø 2,5-3,5mm cableø 2,5-3,5mm</p>	
<p>HARAX® M8-S</p> <p>straight version, 3-poles for 0,14 - 0,34 mm²</p> 	21 02 151 1305			
<p>straight version, 4-poles for 0,14 - 0,34 mm²</p> 	21 02 151 1405		 <p>Gesamtlänge im verschraubten Zustand ca. 40,8mm/ complete length when assembled app. 40,8mm</p> <p>SW9/ width across flats 9</p> <p>View mating side: 3-poles, male version</p> <p>View mating side: 4-poles, male version</p>	
<p>straight version, 3-poles for 0,14 - 0,34 mm²</p> 		21 02 151 2305		
<p>straight version, 4-poles for 0,14 - 0,34 mm²</p> 		21 02 151 2405		