






CE



DG390-5.0

PCB LAYOUT



Approval	CE	
Electrical		
Standard	UL	IEC
Rated voltage	300V	250V
Rated current	8A	10A
Wire range	22-18AWG	1.0mm ²
Withstanding voltage	AC2000V/1Min	
Mechanical		
Ambient temperature	-30℃~+120℃	
Strip length	8-9mm	
Dimensions		
Pitch	5.0mm(.197")	
Poles	2P,3P-24P	
Material		
Housing	PBT,UL94V-0	
Pin header	Brass,Tin plated	
Wire guard	Stainless steel	

HOW TO ORDER :




Series number

No. of pole

1	Single pitch
2	Double pitch

Color

1 Grey	4 Green	7 Trans Parent
2 Blue	5 Orange	8 Yellow
3 Black	6 Red	9 White



NAME

DG390-5.0