

# 型号说明 Ordering Information

IRS-101-1A3D-R/B

- 基座颜色 Base color
- 盖帽颜色 Cap color
- 直流灯 DC lamp
- 盖帽标记 Cap marking
- 盖帽种类 Cap option
- 产品序号 Product order
- 电路特性 Circuitry trait
- 刀数 Poles
- IRS带灯波动开关 Illuminated Rocker Switch
- RS不带灯波动开关 Rocker Switch

# 技术特性 Specification

1. 规格 Rating: 20A 125VAC; 15A 250VAC; 35A 12VDC
2. 接触电阻 Contact Resistance: 35mΩ max
3. 绝缘电阻 Insulation Resistance: 500VDC 100MΩ min
4. 耐电压 Dielectric Strength: 1500VAC, 1M/minute
5. 操作温度 Operating Temperature: -25°C ~ +85°C
6. 电气寿命 Electrical Life: 10,000 Cycles

## 电路特性 Circuitry trait

01	ON	—	OFF
02	ON	—	ON
11	(ON)	—	OFF
03	ON	OFF	ON
13	ON	OFF	(ON)
23	(ON)	OFF	(ON)
( ): 回弹指示 Indicates Momentary			


## 盖帽颜色 Cap color

黑 Black (B)  
 白 White (W)  
 红 Red (R)  
 黄 Yellow (Y)  
 绿 Green (G)  
 蓝 Blue (BL)  
 桔黄 Orange (O)  
 灰 Gray (GR)


## 基座颜色 Base color

黑 Black (B)  
 白 White (W)  
 灰 Gray (GR)

## 盖帽种类 Cap option



## 盖帽标记 Cap marking



## 防水罩 Water proof cap

