



JKL PART NUMBER	-A- LENGTH	LCD HIGH OUTPUT WHITE RGB COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) MINIMUM
BF2661-24B	61±1.0**	9,400°k x = .285 ± .03 y = .283 ± .03	490 @ 0°C	195	5 ± 1	30,000 TYP.	20,000
BF26180-24B	180±3.0		975 @ 0°C	390			
BF26188-24B	188±3.0		1115 @ 0°C	405			
BF26214-24B	214±2.0**		1150 @ 0°C	445			
BF26230-24B	230±3.0		1240 @ 0°C	495			
BF26240-24B	240±3.0		1290 @ 0°C	515			
BF26250-24B	250±1.5		1350 @ 0°C	540			

**NOTES:**

\* RATED LIFE IS DEFINED AS THE POINT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

\*\* LEAD LENGTH 15±3.0.

RATINGS AT 25°C UNLESS OTHERWISE SPECIFIED.

<b>METRIC</b>  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>							
<b>E</b> CHANGE LEAD LENGTH TO 15±2 1/28/20 <b>D</b> RATED LIFE HRS MINIMUM & 20,000 - & MARKUP 8/5/09 <b>C</b> CORRECT x & y TOLERANCE 7/5/06 <b>B</b> LENGTH TOLERANCE CHANGE ON BF26250-24B 2/3/06 <b>A</b> ELECTRICAL CHANGES & ADD PART BF2661-24B 10/20/04 RELEASED TO CAD MULTI LIST 8/14/03		DRAWN BY L. WENGSTROM APPV'D BY S.N. DATE 1/28/20		TITLE <b>MINIATURE COLD CATHODE FLUORESCENT LAMP</b>		SIZE <b>A</b> FSCM NO. <b>55335</b> DRAWING NO. <b>BF 26-24B</b>					
REV. NO. DESCRIPTION/ECO NUMBER APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE <b>NONE</b>		RELEASED DATE <b>8/14/03</b>		REVISION DATE <b>1/28/20</b>		REV. NO. <b>E</b> SHEET <b>1</b> OF <b>1</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## JKL Components:

[BF2661-24B](#) [BF26230-24B](#) [BF26180-24B](#)