



Specifications:

Contact rating: 3A, 125V AC (50/60Hz)
 Contact resistance: 20mOhm max.
 Insulation resistance: 100MOhm min. at 500V DC
 Dielectric strength: 500V AC for 1 minute
 Mechanical life: 10 000 cycles
 Operating force: 350 +/-150gf
 Timing: non-shorting
 Material: Frame: stainless steel
 Box / pressure finger: phenolic resin
 Actuator: polycarbonate
 Terminal / contact: copper, silver plated



Tolerances: ±0.3mm	Date	Name	<h1>MFS 106 D</h1>
	03/11	dr	
			<h2>30 23 17</h2>
			Page
			1/1
Modifications	Date	Name	

knitter-switch