



ENGLISH

Datasheet

RS Pro Swivel Plate Castor PR100ASF, 75kg

RS Stock No: **666-7567**



Product Details

RS Pro swivel castor has load capacity of 75 kg. A range of rubber tyred silent running castors come with a built-in synthetic thread guard.

Features and Benefits

- Silent running castors
- Precision ball bearing in wheel
- Reduces noise in the workplace
- Grey rubber tyre



ENGLISH

Specifications:

| | |
|-------------------------|-----------------|
| Features | Quiet Operation |
| Fixing Centres (Length) | 80 mm |
| Fixing Centres (Width) | 60 mm |
| Fixing Centres | 80 x 60 mm |
| Fixing Hole Size | 9 mm |
| Fixing Plate Dimensions | 100 x 85 mm |
| Fixing Plate Length | 100 mm |
| Fixing Plate Width | 85 mm |
| Hub Bearing Type | Ball Bearing |
| Hub Material | PP |
| Includes Brake | No |
| Load Capacity | 75 kg |
| Number of Fixing Holes | 4 |
| Overall Height | 140 mm |
| Rotation | Swivel |
| Tyre Material | Rubber |
| Weight Class | Light Duty |
| Wheel Diameter | 100 mm |
| Wheel Width | 30 mm |