

Datasheet

Brass Pneumatic Quick Connect Coupling, G 1/4 Female, Threaded

RS Stock number 667-1692



SERIE 017

PNEUMATIC COUPLINGS
PNEUMATISCHE KUPPLUNGEN

←→ ←→ SUPER FLOW LINE SUPERDURCHFLUSS

Interchangeability - Kompatibilität
SCHRADER NWS, RECTUS 17

Temperature Range Temperaturbereich
-20 °C +100 °C (-4 °F +212 °F)

Working Pressure - Betriebsdruck
0 - 35 bar (0 - 508 PSI)

Flow capacity - Nennweite
NW - 5

Option - Optionen
K - Chrome plated - verchromt
N - Nickel plated - vernickelt (standard)
V - Viton Seal - Viton Dichtung

For optional orders please add the symbol of your option end of the order no. Bei Optionsbestellungen Kennbuchstabe bitte hinzufügen (Beispiel: 017 EG 13-K-V)

Material - Material

Coupler Body - Kupplungsgrundkörper : Brass Nickel Plated - Messing Vernickelt

Back Part - Rückwärtiger : Steel Nickel Plated - Stahl Vernickelt

Sleeve - Hülse : Steel Nickel Plated - Stahl vernickelt

Valve - Vent : Zinc Diecasting & Nickel Plated - Zinkdruckguß, verzinkt


Springs - Federn : Stainless Steel - Edelstahl

Locking O-Ring - Sprengling : Stainless Steel - Edelstahl

Balls - Kugeln : Stainless Steel - Edelstahl AISI 420

Seals - Dichtungen : Nitrile - NBR (Ni)

Plug - Nippel : Steel Nickel Plated - Stahl vernickelt



Couplers and Plugs
Kupplungen und Nippel

Connection Anschlüsse | Order No Bestellnr. | SW | L | ØD



Male Thread Coupling
Kupplung mit Aussengewinde

BSPT 1/4"	017 RG 13	19	58	23
BSPT 3/8"	017 RG 17	19	58	23
BSPT 1/2"	017 RG 21	22	48	23



Female Thread Coupling
Kupplung mit Innengewinde

BSP 1/4"	017 DG 13	19	53	23
BSP 3/8"	017 DG 17	19	53	23
BSP 1/2"	017 DG 21	24	53	23




Standard Hose Barb Coupling
Kupplung mit Schlauchhülse

6 mm - 1/4"	017 HG 06	19	69	23
8 mm - 5/16"	017 HG 08	19	69	23
9 mm - 5/14"	017 HG 09	19	69	23
10 mm - 3/8"	017 HG 10	19	69	23
13 mm - 1/2"	017 HG 13	19	69	23



Plastic Hose Coupling
Kupplung für Kunststoffschlauch

6x8 mm - M 12x1	017 PG 06	19	58	23
8x10 mm - M 16x1	017 PG 08	19	58	23
9x12 mm - M 16x	017 PG 09	19	58	23



Plastic Hose Couplings With Spring
Kupplung für Kunststoffschlauch mit Knickstützfeder

6x8 mm - M 12x1	017 YG 06	19	155	23
8x10 mm - M 16x1	017 YG 08	19	165	23
9x12 mm - M 16x1	017 YG 09	19	170	23




Standard Hose Barb Plugs
Nippel mit Schlauchhülse

6 mm - 1/4"	017 HU 06		51	
8 mm - 5/16"	017 HU 08		51	
10 mm - 3/8"	017 HU 10		51	




Plastic Hose Plugs
Nippel für Kunststoffschlauch

6x8 mm - M 12x1	017 PU 06		43	
8x10 mm - M 16x1	017 PU 08		46	
9x12 mm - M 16x1	017 PU 09		46	



Male Thread Plug
Nippel mit Aussengewinde

BSPT 1/8"	017 RU 10	12	38	
BSPT 1/4"	017 RU 13	14	41	



Female Thread Plug
Nippel mit Innengewinde

BSP 1/8"	017 DU 10	12	38	
BSP 1/4"	017 DU 13	17	41	
BSP 3/8"	017 DU 17	19	41	
BSPT 1/2"	017 DU 21	24	41	