



ENGLISH

Datasheet

Brass Pneumatic Quick Connect Coupling, R 1/2 Male, Threaded

RS Stock number 6671740



Features

Interchangeability: PCL STANDARD Series, Rectus 19

Temp.Range: - 20°C +100°C

Working Pressure: 0 -35 bar (0 - 508 PSI)

Flow Capacity: NW - 5.5

Option: F=Through Flow - passage libre, C= Steel (coupler body), K= Chrome plated, V= Viton Seal Material

Coupler Body/Sleeve/Valve: Brass Nickel Plated

Springs: Stainless Steel

Locking O-Ring: Stainless Steel

Balls: Stainless Steel

Seals: Nitrile NBR

Plug: Brass Nickel Plated