


Datasheet

# Brass Pneumatic Quick Connect Coupling, Hose Barb, 4mm Hose Barb Connection

RS Stock number 667-1813

## 021 [Quick Release Pneumatic Couplings]



### Interchangeability

RECTUS 2 RECTUS 90,  
CAMOZZI

### Temperature Range

-20 C +100 C ( -4 F +212 F )

### Working Pressure

0 - 35 bar ( 0 - 500 PSI )

### Flow Capacity

NW - 5

### Standard version

Balls : Stainless Steel  
Buna ( N )

### Options

F-Straight Through flow

K - Chrome Plated

N - Nickel Plated

T - NPTF Thread

V - Viton Seal

### Material

Coupler Body : Brass Nickel Plated

Sleeve : Steel Body : Brass Nickel Plated

Valve : Brass

Springs : Stainless Steel


Locking O-Ring : Stainless Steel

Balls : Stainless Steel

Seals : Buna ( N )


Plug : Brass Nickel Plated

### Couplers and Plugs








Male Thread Coupler





Connection	Order No	SW	Length	Dia
g 1/8"	021 EG 10	14	36	16
G 1/4"	021 EG 13	17	38	16
G 3/8"	021 EG 17	19	38	16
M 12X1,5	021 EG 12	17	39	16
M 14X1,5	021 EG 14	17	39	16






Female Thread Coupler

G 1/8"	021 DG 10	14	36	16
G 1/4"	021 DG 13	17	38	16
G 3/8"	021 DG 17	19	38	16
M 12X1,5	021 DG 12	17	38	16
M 14X1,5	021 DG 14	17	38	16

 Standart Hose Barb Coupler	4mm 1/6"	021 HG 04	14	46	16
	6mm 1/4"	021 HG 06	14	46	16
	8mm 5/16"	021 HG 08	14	46	16
	9mm 5/14"	021 HG 09	14	46	16
	10mm 3/8"	021 HG 10	14	46	16
 Plastic Hose Coupler	6mm Parker 1/4"	021 HG 06 P	14	46	16
	4X6mm-M10X1	021 PG 04	14	41	16
 Plastic Hose Coupler With Spring	6X8mm-M10X1	021 PG 06	14	41	16
	4X6mm-M10X1	021 SG 04	14	53	16
 Standart Hose Barb Plug	6X8mm-M12X1	021 SG 06	17	53	16
	4mm-M10X1	021 MG 04	14	60	16
	5mm-M12X1	021 MG 05	14	60	16
	6mm-M12X1	021 MG 06	17	60	16
 Plastic Hose Plug	6mm-M12X1	021 MG 08	17	60	16
	4X6mm-M10X1	021 YG 04	14	125	16
	6X8mm-M10X1	021 YG 06	14	130	16

 <p>Male Thread Plug</p>	4mm 1/6"	021 HU 04	32	9
	5mm 1/5"	021 HU 05	32	9
	6mm 1/4"	021 HU 06	32	9
	8mm 5/16"	021 HU 08	32	9
	9mm 5/14	021 HU 09	33	12
	10mm 3/8"	021 HU 10	33	12
	6mm Parker	021 HU 06 P	36	16
 <p>Female Thread Plug</p>	4X6 mm- M10X1	021 PU 04	32	10
	6X8 mm- M12X1	021 PU 06	32	12
 <p>Male Thread Plug</p>	4X6mm- M10X1	021 SU 04	14	44
	6X8mm- M12X1	021 SU 06	17	44
 <p>Male Thread Plug</p>	4 mm- M10X1	021 MU 04	14	50
	5 mm- M10X1	021 MU 05	14	50
	6 mm- M12X1	021 MU 06	14	50
	8 mm- M12X1	021 MU 08	14	50
	9 mm- M12X1	021 MU 09	14	50
	10 mm- M14X1	021 MU 10	17	50


**Male Thread Plug**
**4X6mm-**
**021 YU 04**
**115**
**M10X1**
**6X8 mm-**
**021 YU 06**
**120**
**M10X1**

**Male Thread Plug**
**G1/8"**
**021 EU 10**
**14**
**25**
**G1/4"**
**021 EU 13**
**17**
**28**
**G3/8"**
**021 EU 17**
**19**
**28**
**M 10X1**
**021 EU 10 M**
**14**
**26**
**M 12X1,5**
**021 EU 12**
**17**
**28**
**M 14X1,5**
**021 EU 14**
**17**
**28**

**Male Thread Plug**
**G 1/8"**
**021 DU 10**
**14**
**25**
**G 1/4"**
**021 DU 13**
**17**
**26**
**G 3/8"**
**021 DU 17**
**19**
**27**
**M 10X1**
**021 DU 10 M**
**14**
**27**
**M 12X1,5**
**021 DU 12**
**17**
**27**
**M 14X1,5**
**021 DU 14**
**17**
**27**