



ENGLISH

Datasheet

Brass Pneumatic Quick Connect Coupling, Hose Barb, 6mm Hose Barb Connection

RS Stock number 6671866



Features

Interchangeability: Rectus 2, Rectus 90, Camozzi

Temp.Range: -20°C to +100°C

Working Pressure: 0-35 bar (0-500 PSI)

Flow Capacity: NW -5.5

Options: F - straight thru flow

N - Nickel Plated

T - NPTF Thread

V - Viton Seal

Material

Coupler Body - Brass Nickel Plated

Sleeve - Steel Body : Brass Nickel Plated

Valve - Brass

Springs - Stainless Steel

Locking O-Ring Stainless Steel

Balls - Stainless Steel

Seals - Buna (N)

Plug - Brass Nickel Plated

Standard Version:

Balls: Stainless Steel

Buna (N)