



Datasheet

ENGLISH

Brass Pneumatic Quick Connect Coupling, Hose Barb, 8mm Hose Barb Connection

RS Stock number 6671891



Features

Interchangeability: RECTUS 23, FORSTER, CEJN 310,
US MIL SPECC 4109 1/4", HANSEN 3000 PARKER PBF
1/4 TST 024 ATLAS COPCO QIC 08

Options:

C Chrome Plated

N Nickel Plated

K Chrome Plated

V - Viton Seal

Temperature Range: -20 C +100 C (-4 F +212 F)

Flow Capacity: NW - 5 .5

Working Pressure: 0-35 bar (0-500PSI)

Material:

Coupler Body : Brass Nickel Plated

Back part : Brass Nickel Plated

Working Pressure: 0 - 35 bar (0 - 500 PSI)

Sleeve : Steel Nickel Plated

Valve: Brass

Springs : Stainless Steel

Standard version: Nickel Plated, Buna (M)

Locking O-Ring : Stainless Steel

Nickel Plated Balls : Stainless Steel AISI 420

Seals: Buna (M) :

Plug : Steel Nickel Plated

Standard Version

Nickel Plated, Buna (M)