



RE932-07ST

- Epoxy fibre-glass FR4 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au with solder stop mask
- Adaption circuit board for SO 24-w designed in a single row
- Pitch: 1.27 mm (295 mil)
- Hole diameter 1.00 mm
- Size 21.00 x 32.00 mm