

Datasheet


Brass Pneumatic Quick Connect Coupling, G 1/2 Male, Threaded

RS Stock number 667-1992

026 [Quick Release Pneumatic Couplings]



SUPER FLOW LINE



Interchangeability

TST 025, RECTUS 25, PARKER PE
RECTUS 26, CEJN 320, JWL 520,
JWL 530

Temperature Range

-20 C +100 C (-4 F +212 F)

Working Pressure

0 - 35 bar (0 - 500 PSI)

Flow Capacity

NW - 7,5

Standard version

Brass Nickel Plated
Buna (M)


Options

F - Straight Flow
K - Chrome Plated
N - Nickel Plated
S - Stainless Steel
V - Viton Seal

Material


Coupler Body : Laiton Brass
Sleeve : Laiton Brass
Valve : Laiton Brass
Springs : Stainless Steel
Locking O-Ring : Stainless Steel
Pims : Stainless Steel
Seals : Buna (M)
Plug : Brass Nickel Plated

Couplers and Plugs








Male Thread Coupler





Connection	Order No	SW	Lenght	Dia
G 1/8"	026 EG 10	21	41	25
G 1/4"	026 EG 13	21	41	25
G 3/8"	026 EG 17	21	41	25
G 1/2"	026 EG 21	21	44	25
M 14X1,5	026 EG 14	21	42	25
M 16X1,5	026 EG 16	21	43	25
M 18X1,5	026 EG 18	21	43	25




Female Thread Coupler


G 1/4"	026 DG 13	21	41	25
G 3/8"	026 DG 17	21	41	25
G 1/2"	026 DG 21	24	41	25
M 14X1,5	026 DG 14	21	44	25
M 16X1,5	026 DG 16	21	41	25
M18X1,5	026 DG 18	22	41	25

 Standart Hose Barb Coupler	6 mm 1/4"	026 HU 06	21	55	25
	8 mm 5/16"	026 HU 08	21	55	25
	9 mm 5/14 "	026 HU 09	21	55	25
	10 mm 3/8"	026 HU 10	21	55	25
	13 mm 1/2"	026 HU 13	21	55	25
 Standart Hose Barb Coupler	6 mm Parker 1/4"	026 HG 06 P	21	55	25
	10 mm Parker 3/8"	026 HG 10 P	21	58	25
	13 mm Parker 1/2"	026 HG 13	21	62	25
 Plastic Hose Coupler	6x8mm-m12x1	026 PG 06	21	60	25
	8x10mm- M16x1	026 PG 08	21	63	25
	9x12mm- M16x1	026 PG 09	21	72	25
 Panel Mound Standart Hose Coupler	6 mm-M12x1	026 MG 06	21	60	25
	8 mm-M12x1	026 MG 08	21	63	25
	10 mm-G1/4"	026 MG 10	21	72	25
 Plastic Hose Coupler With Spring	6X8mm- M12X1	026 YG 06	21	133	25
	8x10mm- M16x1	026 YG 08	21	148	25
	9x12mm- M16x1	026 YG 09	21	148	25

	6 mm 1/4"	026 HU 06		46
	8 mm 5/16"	026 HU 08		46
	9 mm 5/14"	026 HU 09		46
	10 mm 3/8"	026 HU 10		46
	13 mm 1/2"	026 HU 13		46
 Standart Hose Barb	6 mm Parker 1/4"	026 HU 06 P		43
	10 mm Parker 3/8"	026 HU 10 P		46
	13 mm Parker 1/2"	026 HU 13 P		50
 Plastic Hose Plug	4X6-mm- M10X1	026 PU 04		34
	6X8mm- M112x1	026 PU 06		34
	8x10mm-12x1	026 PU 08		42
	3x12mm- M16x1	026 PU 09		42
 Panel Mound Standard Hose Plug	6 mm-M12x1	026 MU 06	14	56
	8 mm-M12x1	026 MU 08	14	56
	10 mm-M14x1	026 PU10	17	56
 Plastic Hose Plug With Spring	4X6mm- M10X1	026 YU 04		120
	6X8mm- M12x1	026 YU 06		120
	8x10mm- M16x1	026 YU 08		140
	9x12mm- M16x1	026 YU 09		140


Male Thread Plug

G 1/8"	026 EU 10	13	33
G 1/4"	026 EU 13	14	37
G 3/8"	026 EU 17	17	37
G 1/2"	026 EU 21	22	43
M 14X 1,5	026 EU 14	17	34
M 16X 1,5	026 EU 16	19	36
M 18X1,5	026 EU 18	19	37


Female Thread Plug

G 1/8"	026 DU 10	14	32
G 1/4"	026 DU 13	17	33
G 3/8"	026 DU 17	19	33
G 1/2"	026 DU 21	24	36
M 14X1.25	026 DU 14-1	17	33
M 14X1,5	026 DU 14	17	33
M 16X1,5	026 DU 16	19	33
M 18X1,5	026 DU 18	22	36


2 way coupler

G 3/8"	026 2G 17
G 1/2"	026 2G 21


3 way coupler

G 3/8"	026 3G 17
G 1/2"	026 3G 21