

## Torque wrench

### 730 Quick



Art.No. 50184004  
GTIN 4018754292660  
Model 730/4 QUICK



**Label.** Torque wrench No. 730 Quick Values only for in-lb 8-40Nm Inside square stitch size 9x12 mm L. 223mm

- Description.**
- click-type
  - the measuring element is only under load while force is being applied, no need for manual reset to zero
  - mount for interchangeable insert/shell tools
  - QuickRelease safety lock (sizes 5–65)
  - rapid setting thanks to easy-action locking lever in the handle (sizes 5–65)
  - ergonomically designed, non-slip adjuster with a thumb recess
  - magnifying glass integrated in the display window
  - optimised convex handle for strain-free working
  - dual stop signal
  - twin scales N·m/ft·lb and N·m/in·lb (sizes 5–80)
  - on request also available as an N·m-only version without twin scale (sizes 5–65)
  - can be applied for either clockwise or anticlockwise tightening by turning the inserts over
  - any force applied to the tool after the 'click' or applied in the opposite direction to the current function – e.g. forcible loosening of a jammed screw - does not act on the trigger mechanism and cannot cause damage to it
  - calibration using perfectControl® calibrating unit No 7794 or calibration system No 7706. Readjustment does not require disassembly.
  - certificate in accordance with DIN EN ISO 6789-2:2017
  - **display deviation value ± 4%**

## Advantages.

Quick adjustment thanks to easy-to-operate clamping lever in handle


Ergonomically shaped, non-slip adjustment element with thumb recess and optimised ball handle for fatigue-free work

Efficient. No reset to "0" necessary, as measuring element is only strained during the tightening process

Releasing torque wrench with receptacle for exchangeable plug-in tools, double stop signal (tactile and audible), left-hand tightening by turning over the plug-in tools



## Technical Drawing.



## Technical Attributes.

Breite mm (b)	27,5 mm
Size	4
Size hexagon socket [internal square]	9x12 mm
Height mm (h)	23,6 mm
Länge mm (l)	223 mm
LF	200,8 mm
Measuring range N·m	8-40 N·m
SF	17,5 mm
Scale division [E1]	1 N·m

## Logistics data.

Length (IFS)	225
Width (IFS)	43
Height (IFS)	30
Length (packed, mm)	255
Width (packed, mm)	55
Höhe (verpackt, mm)	55
Code	50184004
Weight	395 g
Weight (gross, kg)	0,478
Weight PAP (kg)	0,000
Weight PVC (kg)	0,066
GTIN	4018754292660
Numbers of content units per order units	1
Country of origin	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82041100

## Varianten.

Code	Article number (ERP)	Article description (Autom.)	GTIN
91381054	730/2 1 QUICK	Torque wrench No. 730 Quick Values only for in-lb 2-10Nm Inside square stitch size 9x12 mm L. 179mm	4018754320325
50184002	730/2 QUICK	Service MANOSKOP torque wrench No. 730 Quick Values only for in-lb 4-20Nm Inside square stitch size 9x12 mm L. 179mm	4018754292653
50184004	730/4 QUICK	Torque wrench No. 730 Quick Values only for in-lb 8-40Nm Inside square stitch size 9x12 mm L. 223mm	4018754292660
50584001	730A/2-1 QUICK	Torque wrench No. 730 Quick Values only for in-lb 17,5-87,5in lb Inside square stitch size 9x12 mm L. 179mm	4018754292677
50584002	730A/2 QUICK	Torque wrench No. 730 Quick Values only for in-lb 30-175in lb Inside square stitch size 9x12 mm L. 179mm	4018754292684
50584004	730A/4 QUICK	Torque wrench No. 730 Quick Values only for in-lb 70-350in lb Inside square stitch size 9x12 mm L. 223mm	4018754292691

## GTIN-Code.



## Accessories.



58250004  
Fine tooth insert  
ratchet



58253004  
QuickRelease ratchet  
insert tool

## Spare parts.



92057436

2 component handle

**STAHLWILLE Eduard Wille GmbH & Co. KG**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-200  
info@stahlwille.de · www.stahlwille.de · Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal  
Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal