

Han PushPull PFT metal Bulkhead Cat.6



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 225 0311
Specification	Han PushPull PFT metal Bulkhead Cat.6
HARTING eCatalogue	https://b2b.harting.com/09352250311

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	RJ45
Element	Panel feed trough set
Specification	AIDA compliant
Features	Intuitive locking mechanism

Version

Locking type	PushPull
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Fixing	Screwable to cover plates
Pack contents	incl. bulkhead mounted housing for rectangular panel cut out, flat seal and HARTING RJ Industrial® 10G RJ45 bulkhead

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm ² Stranded 0.26 ... 0.32 mm ² Solid
Rated current	1.75 A
Rated voltage	50 V
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67



Pushing Performance

Technical characteristics

Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	10 Gbit/s

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 60603-7 Mating face
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	42.4 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440101 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09352250311](#)