

## Coaxial PCB Connector 92\_MMBX-S50-0-12/111\_N

### Description

Edge mount PCB jack

Interface Standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 12.4 GHz

#### Mechanical Data

Board mounting type edge mount  
Weight 0.0011 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

### Related Documents

Outline drawing DOU-00013388  
Catalogue drawing DCA-00013390  
Mounting hole DOU-00013391

### Ordering Information

Tape and Reel package 92\_MMBX-S50-0-12/111\_NM  
Single package 92\_MMBX-S50-0-12/111\_NE

### Remarks

PCB connector without stand-offs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[92\\_MMBX-S50-0-12/111\\_NE](#)