

Item no.: 2002-2207  
 Product description: Double deck terminal block 4-conductor earth PE without marker carrier housing color: green-yellow internal commoning suitable for Ex e applications



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Pollution degree	3
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Number of levels	2
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.25 - 4 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Weight	13.489 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	52 mm
Height	2.047 in

Width	5.2 mm
Width	0.205 in
Depth	70 mm
Depth	2.76 in
Strip length from	10 mm



Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2002-2207	CCA	NL6387			0,2-2,5/4
2002-2207	CSA	154112-1536069			22-12
2002-2207	GL	6187-05HH			4,0
2002-2207	KEMA	NL2116586.02			0,2-4
2002-2207	LR	91/20112(E6)			4,0
2002-2207	PTB	IECExPTB03.0004U			0,2-4
2002-2207	PTB	PTB03Atex1162U			0,2-4
2002-2207	RosTest	8189158			0,2-4
2002-2207	UR	E45172			22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected