


# S/FTP Cat. 6A LSZH patch cord, green, 30 m

PP6A-LSZHCU-G-30M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts



## Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A
- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

## Packaging

Q'ty in crtn, pcs	10
Crtn volume, CUM	0.03
Crtn weight, kgs	9.17
Individual package size LxWxH:	290x215x50 mm
Carton size LxWxH:	380x315x250 mm
Country of origin	CN
Barcode	8716309126465
Customs code	8544421000

## Specifications

Patch cord category 6A SSTP (shielded)  
Length: according to the item  
Structure: AWG 27 (7 x 0.135 mm wire), COPPER  
FM-PE insulation of the wire: 1.0 mm  
With LDPE filler  
With polyester tape  
With aluminum foil  
Drain hose: not used  
With Braid : 16 x 4/0.12mm  
Outer insulation: 5.8 mm  
Color: according to the item  
Operation up to 500 MHz

## Certificates

