

## 6-1460820 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



### MMCX RF Connectors

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Jack
- ? Terminate To Printed Circuit Board
- ? Body Style = Straight
- ? Surface Mountable

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**6-1460820 -1**

[Active](#)

[View 3D PDF](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [smt jack](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files: ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [3D Model](#) (STEP, Version A)

#### Additional Information:

- ? [Product Line Information](#)

#### Additional Product Images:

- ? [Schematic](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Product Type = Jack
- ? Body Style = Straight

#### Mechanical Attachment:

- ? Surface Mountable = Yes

#### Electrical Characteristics:

- ? Connector Impedance (?) = 50

#### Configuration Related Features:

- ? Bulkhead Jack = No

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Terminate To = Printed Circuit Board

#### Packaging Related Features:

- ? Packaging Method = Tape & Reel
- ? Packaging Quantity = 750

#### Other:

- ? Brand = AMP