

## J.H - 3/8" metric 6-point sockets




### **Standards:**

**NF ISO 2725-1, NF ISO 1711-1,  
ISO 2725-1, ISO 1711-1, DIN  
3124, ASME B107.5**

### **Description:**

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

	A [mm]	Hex Size [mm]	Diameter [mm]	Diameter D1 [mm]	Length L [mm]	Length L1 [mm]	Weight [g]
J.10H	10.0	6.0	17.6	14.7	27.0	7.8	26.0
J.11H	11.0	6.0	17.6	16.0	27.0	9.0	27.0
J.12H	12.0	6.0	17.6	17.2	27.0	9.5	26.0
J.13H	13.0	6.0	17.4	18.3	30.0	10.4	36.0
J.14H	14.0	6.0	17.6	19.5	30.0	10.5	34.0
J.15H	15.0	6.0	18.9	20.8	30.0	12.0	38.0
J.16H	16.0	6.0	19.9	22.0	30.0	12.0	45.0
J.17H	17.0	6.0	21.7	23.4	30.0	13.0	52.0
J.18H	18.0	6.0	21.7	24.7	33.0	13.0	69.0
J.19H	19.0	6.0	22.7	26.0	33.0	14.0	62.0
J.20H	20.0	6.0	22.2	27.2	33.0	15.0	70.0
J.21H	21.0	6.0	23.5	28.5	33.0	16.0	75.0
J.22H	22.0	6.0	24.7	29.7	33.0	16.5	80.0
J.23H	23.0	6.0	26.0	31.0	33.0	16.5	90.0
J.24H	24.0	6.0	26.3	31.3	33.0	16.5	86.0
J.7H	7.0	6.0	17.6	11.0	27.0	6.0	24.0
J.8H	8.0	6.0	17.6	12.2	27.0	6.5	25.0
J.9H	9.0	6.0	17.6	13.5	27.0	6.7	25.0