


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2233)
PRT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PRT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

REV						DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE							
												PAN-TY® RELEASABLE LASHING TIES							
												CUSTOMER DRAWING							
												ITEM REVISION NAME		10B015LA/01		PANDUIT			
												DATASET FILE NAME		10B015LA/00 SS-6507_REV09					
												UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: [IN mm]				MATERIAL:			
												.x : .1 (2.5) .xxx : .010 (.25)				NYLON 6.6			
												.xx : .02 (.5) ANGLES : - - - - -							
												DRAWING NUMBER:		SS - 6507		THIRD ANGLE PROJECTION			
												DRAWN BY		DATE			CHK	SCALE	SHT 1 OF 1
												L.VALDES		7-15-77		HVP	NONE		

2

1

D10100DA/16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PRT6EH-Q0](#) [PRT2EH-C0](#) [PRT2EH-Q0](#) [PRT5EH-C0](#) [PRT8EH-C0](#) [PRT5EH-C](#) [PRT10EH-C](#) [PRT6EH-C](#) [PRT6EH-C0](#) [PRT12EH-C0](#) [PRT10EH-C0](#)