

3609 - MALE STUD ELBOW BSP TAPER



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
sub-base	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	C	F (mm)	ØG (mm)	H (mm)	J (mm)	K (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3609 04 10	4	R1/8	13	10	15	7		18	.014
3609 04 13	4	R1/4	14	10	17	7		18	.02
3609 06 10	6	R1/8	13	12	17.5	8		21.5	.018
3609 06 13	6	R1/4	14	12	19	8		21.5	.025
3609 08 10	8	R1/8	13	15	19.5	10		23.5	.022
3609 08 13	8	R1/4	14	15	21	10		23.5	.029
3609 08 17	8	R3/8	17	15	21	10		23.5	.035
3609 10 13	10	R1/4	15	17.5	23.5	12		29	.037
3609 10 17	10	R3/8	17	17.5	25.5	12		29	.043
3609 12 13	12	R1/4	15	19.5	26	15		31	.049
3609 12 17	12	R3/8	17	19.5	28.5	15		31	.055
3609 12 21	12	R1/2	21	19.5	28.5	15		31	.072
3609 14 17	14	R3/8	19	21.5	29	16		34	.063
3609 14 21	14	R1/2	22	21.5	30	16		34	.072