

# M10/10.P



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

## General Information

<b>Extended Product Type:</b>	M10/10.P
<b>Product ID:</b>	1SNA165115R1000
<b>EAN:</b>	3472591651157
<b>Catalog Description:</b>	M10/10.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
<b>Long Description:</b>	- Reliable electrical and mechanical contact with the rail, - Flexibility: snap onto symmetrical and asymmetrical rails.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>CSA Certificate:</b>	1SND161039A0201
<b>Color:</b>	Green-Yellow
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 20 ... 6 AWG
<b>Connecting Capacity UL/CSA:</b>	Screw Clamp / Rigid 20 ... 6 AWG Stranded 6 AWG
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5 ... 16 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 6 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>Data Sheet, Technical Information:</b>	1SNC160019C0202
<b>Declaration of Conformity - CE:</b>	1SND225017U1000
<b>E-nummer:</b>	2925527
<b>EAC Certificate:</b>	1SND161009A1100
<b>EAN:</b>	3472591651157
<b>ETIM 4:</b>	EC000901 - Ground terminal block
<b>ETIM 5:</b>	EC000901 - Ground terminal block
<b>ETIM 6:</b>	EC000901 - Ground terminal block
<b>Environmental Information:</b>	1SND220004E1002
<b>Flammability According to UL94:</b>	V0
<b>Function:</b>	Ground
<b>Gauge Type:</b>	B6
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SNC160019C0202
<b>Insulation Material:</b>	Polyamide
<b>Invoice Description:</b>	M10/10.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
<b>Minimum Order Quantity:</b>	50 piece
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Connections:</b>	2
<b>Number of Levels:</b>	1
<b>Object Classification Code:</b>	x

<b>Order Multiple:</b>	50 piece
<b>Package Level 1 EAN:</b>	3472591651157
<b>Package Level 1 Gross Weight:</b>	1.45 kg
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Length:</b>	220 mm
<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	101 mm
<b>Package Level 2 Gross Weight:</b>	14.850 kg
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Units:</b>	500 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 3 Units:</b>	24000 piece
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	M10/10.P
<b>Product Name:</b>	Terminal block
<b>Product Net Depth:</b>	40.5 mm
<b>Product Net Height:</b>	43.5 mm
<b>Product Net Weight:</b>	29 g
<b>Product Net Width:</b>	10 mm
<b>Product Packing Type:</b>	Box
<b>RMRS Certificate:</b>	1SND161007A1101
<b>Rated Cross-Section:</b>	10 mm <sup>2</sup>
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 1200 A
<b>Recommended Screw Driver:</b>	5.5 ... 6 mm
<b>RoHS Date:</b>	20050518
<b>RoHS Information:</b>	1SND230023F0208
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	green/yellow Screw Clamp Terminal Blocks M10/10.P
<b>Spacing:</b>	10 mm
<b>Sub-Function:</b>	2 connections
<b>Sub-Function 2:</b>	Screw rail connection
<b>Sub-Function 3:</b>	2 connections
<b>Tightening Torque:</b>	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
<b>Wire Stripping Length:</b>	12.0 mm
<b>cUL Certificate:</b>	1SND161011A0202
<b>Number of Potentials:</b>	1

