



2201 E-2RS1TN9

Dimensions



d	12	mm
D	32	mm
B	14	mm
d_2	≈ 15.5	mm
D_2	≈ 27.34	mm
$r_{1,2}$	min. 0.6	mm

Abutment dimensions



d_a	min.	15.5	mm
d_a	max.	15.5	mm
D_a	max.	27.8	mm
r_a	max.	0.6	mm

Calculation data

Basic dynamic load rating C	6.2	kN
Basic static load rating C_0	1.4	kN
Fatigue load limit P_u	0.08	kN
Limiting speed	16000	r/min
Calculation factor k_r	0.045	
Calculation factor e	0.33	
Calculation factor Y_0	2	
Calculation factor Y_1	1.9	
Calculation factor Y_2	3	

Mass

Mass bearing	0.053	kg
--------------	-------	----